

Cherry Burrell Votator Scraped Surface Heat Exchanger- 6 x 24

Mfg: Cherry Burrell

Model: 6SSHE

Stock No. EECA005.

Serial No. 36080VA

Cherry Burrell Votator Scraped Surface Heat Exchanger- 6 x 24. Model: 6SSHE. S/N: 36080VA. Shell MAWP @ 375 °F: 250 psi. Jacket MAWP @ 375 °F: 150 psi. Equipped with (4) 1-1/2 in. W x 12 in. L bakelite scrapers. Sew-Eurodrive Motor, 3 hp, 1700 rpm, 230/460 V, 8.6/4.3 amps, 60 Hz, 3 phase. Sew-Eurodrive Speed Reducer, 6.98 ratio, 244 rpm (final). Votator scraped surface heat exchangers can be employed in the continuous, closed processing of virtually any pumpable fluid or slurry involving: cooking, slush freezing, cooling, crystallizing, mixing, plasticizing, gelling, polymerizing, heating, and aseptic processing. Inlets: (1) 1-1/2 in. dia. FNPT (media), (1) 2 in. dia. S-line fitting (product). Outlets: (1) 1-1/2 in. dia. FNPT (media), (1) 2 in. dia. S-line fitting (product). Overall dimensions: 72 in. L x 27 in. W x 32-1/2 in. H.



