

1999 Machinefabriek Amersfoort B.V. Presizer PS 600

Mfg: Machinefabriek Amersfoort

Model: PS600

Stock No. GAFF002.

Serial No. 3047

1999 Machinefabriek Amersfoort B.V. Presizer PS 600. Model: PS600. S/N: 3047. Capacity per hour: 6,600 lbs. Cycle time: 18 sec. Pressure: 3,625 psi. Electrical requirements: 16 hp, 460 V, 60 Hz, 3 phase. The Presizer is designed to meet the demand for maximum profitability in the handling of all bones in respect to reduce the length of the bones to 6-8 in. All bones can be put though the system, but it is suggested that back, neck, rib, brisket, and possibly the inner tail (without rind) bones be utilized. Inlets: (1) 24 in. L x 14 in. W infeed. Outlets: (16) 5-1/2 in. W x 5-1/2 in. H ports. Overall dimensions: 9 ft. L x 42 in. W x 67 in. H.



