

Stainless Steel Incline Conveyor

Mfg:

Model:

Stock No. ENAE65058.

Serial No.:

Stainless Steel Incline Conveyor. Maximum product width: 17-1/2 in. W. Belt cleat: 3 in. H. Gap between the paddles of the cleats: 12 in. Baldor Motor, 3/4 hp, 1750 rpm, 90 V, 7.6 amps. Infeed: 40-1/2 in. H. Exit height: 8 ft. 8 in. H. (2) 18 in. W x 18 in. H access doors. Hopper inner dimensions: 45 in. L x 41 in. W x 39 in. deep. Overall dimensions 8 ft. 10 in. L x 45 in. W x 117 in. H.



