

Pacific Packaging Machinery, Inc. 10 Station Rotary Pressure Filler

Mfg: Pacific Packaging Machinery, Inc.

Model:

Stock No: END88294.10

Serial No: 1149

Pacific Packaging Machinery, Inc. 10 Station Rotary Pressure Filler. Serial no. 1149. Throughput capacity: 180 containers per minute depending on size of container. Maximum bottle diameter: 4 in. Maximum bottle height: 6-1/2 in. Conveyor height: 37-3/4 in. Metal link belt: usable length is 96 in. x 3.25 in. W (overall belt length is 204 in. L). Waukesha positive displacement pump: model: P25, serial no: D066710SS. Hub City gear drive: Model: AD2, assembly no: 0220-00302-004. Borg Warner Morse® speed reducer, model: 18GCT, serial no: J82MJ0019, .28 hp, 1750 rpm. This machine initially filled 16-ounce containers of margarine. Overall dimensions: 8 ft. 10 in. L x 4 ft. 6 in. W x 8 ft. 4 in. H.







