

## Fristam Centrifugal Pump

Mfg: Fristam

Model: FPX 3532-130

Stock No. HDMD314.10

Serial No. FPX3532004964

Fristam Centrifugal Pump. Model: FPX 3532-130. S/N: FPX3532004964. Pump capacity: 140 gpm. Baldor Industrial Motor, 7-1/2 hp, 3450 rpm, 230/460 V, 17.6/8.7 amps, 60 Hz, 3 phase. The FPX3532 has a single internal mechanical seal for longer seal life, process temperature: 400°F, product viscosity: 600 cps, maximum inlet pressure: 150 psi, maximum flow rate: 900 gpm, gentle product handling, low maintenance, CIP-able and SIP-able. Typical applications: bottling, cleaning applications/CIP, de-alcoholization, distillation, emulsifying, evaporation, mechanical separation, reverse osmosis, in-line mixing, water conditioning, transfer filtration, extraction, dosing, dialysis, de-gassing, carbonizing, homogenizing, fermentation. Inlet: 2-1/2 in.  $\frac{1}{2}$ sqline. Outlet: 2 in.  $\frac{1}{2}$ sqline. Overall dimensions: 28 in. L x 14 in. W x 17 in. H.

