

## Tri Clover 15 HP Centrifugal Pump Model SP441 0MD-S

Mfg: Tri Clover

Model: SP441 0MD-S

Stock No.: ENDX681.1a

Serial No.: U0462

Tri Clover 15 hp Centrifugal Pump. Model SP441 0MD-S. S/N U0462. Materials of construction: stainless steel. Flow rate for new pump is 765 gpm with required horsepower at 30 ft. head. Impeller diameter: 6-1/2 in. Inlet 3 in. outlet 3 in. 15 hp Motor, 575 volt, 60 Hz, 3 phase. Tri Clover SP pumps are suited to applications in the pharmaceutical, biotechnology, fine chemical, food, beverage and dairy processing industries, where sanitary standards and corrosion resistance are issues. Overall Dimensions: 32 in. L x 24 in. W x 23 in. H. (ACN94a-84).

