

Tri Clover TSR Positive Displacement Pump

Mfg: Tri Clover

Model: TSR4NLS-25MDU0KT-A0

Stock No. HDNN862.10

Serial No. 466714-01

Tri-Clover TSR Positive Displacement Pump. Model: TSR4NLS-25MDU0KT-A0. S/N: 466714-01. 3-A sanitary rated. Capacity: 25 gpm @ 84 psi. Seal option: Single mechanical seals. Baldor Industrial Motor, 5 hp, 1125 rpm, 208-230/460 V, 10.2/6.6 amps, 60 Hz, 3 phase. Reliance Electric Gear Drive, 327 rpm (final). The TSR is designed for thorough CIP cleaning. Another quality is the interchangeability of rotors for additional flexibility when working with a wider range of temperatures and viscosities. Rotor casing is fully swept, minimizing product entrapment. Handles a wide array of viscosities. Inlets/outlets: (2) 2-1/2 in. dia. S-line fittings. Mounted on base with (4) casters for easy positioning. Overall dimensions: 55-1/2 in. L x 20 in. W x 22 in. H.



