

APV Crepaco CIP System


Mfg: APV Crepaco


Model:


Stock No. ENDX696.29



Serial No.:

APV Crepaco CIP System. APV Paraflow Heat Exchanger. Type HXC 6. S/N: 847-817, M/C No: 74658-B. (20) 9 in. W x 33 in. H stainless steel plates. Heating surface area: approx. 41.25 sq. ft. Each plate has approx. 2.06 sq. ft. of surface area. A-3 sanitary rated. APV Puma Centrifugal Pump, S/N: 20026, Size: 3x2. Brook Hanson Motor: 10.0 hp, 3480 rpm, 575 V, 60 Hz, 3 phase. Monarch Liquid Feed System control panel. (3) 300 gallon stainless steel tanks for caustic, rinse, and acid processes. All tanks feature removable hinged lids and Eurogauge probes. Overall dimensions: 14 ft. L x 4 ft. W x 7 ft. H.









CIP Control Panel has : Monarch Liquid Feed System Minneapolis H B Fuller



