

## Fedco Systems Topping Applicator

Mfg: Fedco

Model: 40

Stock No. HDNP192.12a

Serial No. 148

Fedco Systems Topping Applicator. Model: 40. S/N: 148. Unit consists of an 8-1/2 in. dia. x 47-1/2 in. L drum with (52) 1/8 in. grooves that are spaced at a distance of 1/2 in. Clearance between drums and base: 3/8 in. Designed to slide lengthwise on track. Hopper infeed dimensions: 43 in. L x 23 in. W. Hopper discharge dimensions: 32 in. L x 1-1/2 in. W. Control Panel operates the DC motors. Baldor DC Motor (drum), 1/3 hp, 1750 rpm, 90/100/50 V, 3.7/0.4/0.8 amps. Baldor AC Motor (cleaning blades), 1/2 hp, 1725 rpm, 115/208-230 V, 6/2.3-3 amps, 60 Hz, single phase. Overall dimensions: 77-1/2 in. L x 40-1/2 in. W x 26-1/2 in. H.

