

## Bizerba-Werke Fully Automated Slicer with Stacking/Shingling Option

Mfg: Bizerba-Werke

Model: A406FB

Stock No. ENDX715.4a

Serial No. 1258071

Bizerba-Werke Fully Automated Slicer with Stacking/Shingling Option. Model: A406FB. S/N: 1258071. Programmable, continuously variable stroke adjustment from 30 to 55 strokes/minute. Blade diameter 13 inch. Maximum product size (round): 7.08 in. Maximum product size (rectangular): 6.89 in. x 9.45 in. Slice thickness: 0.02-0.47 in. Maximum stacking height: 2.36 in. Blade speed: 266 rpm. Electrical requirements: 120 V, 4.8 amps, 60 Hz, single phase. Overall dimensions: 45 in. L x 31 in. W x 58 in. H. High slicing performance guaranteed and good slicing quality ensured by additional gripper. Variant with stainless steel chain conveyor to feed a receiving tray. The conveyor is quickly and securely attached to the drive unit. If stacking in portions is selected, the belt executes a compensating movement to ensure straight stacks. Slicing is not interrupted when the belt advances. The drive unit combines the support and drive functions for the portion conveyor. The conveyor is easy to detach for simple cleaning. Programmable for the following operations: number of slices, portions, carriage strokes, product size, slice thickness, form of slice presentation, single or double stack, shingling with variable slice spacing from 0.12 to 1.57 inch, flat shingling, slice position. Sharpens blade at the push of a button (via a program).







