

Carrier Air-Cooled Liquid Chiller- 25 Ton

Mfg: Carrier

Model: 30GT-025---600

Stock No. EPBD004.

Serial No. 0494F81110

Carrier Air-Cooled Liquid Chiller- 25 Ton. Model: 30GT-025---600. S/N: 0494F81110. Outdoor use only. Refrigerant: R-22. Test pressure hi/lo: 480/235 psig. System requirements: 460 V, 60 Hz, 3 phase. Carlyle 6-Cylinder Reciprocating Compressor, Model: O6E7265310, S/N: 5293J01747 S/O, semi-hermetic, electrical requirements: 460 V, 43.6 RLA, 60 Hz, 3 phase. (2) Fan Motors, 460 V, 3.1 FLA, 60 Hz, 3 phase. Control requirements: 115 V, 7 amps, 60 Hz, single phase. Aluminum fin/copper tubes. Small in size, big in installation and operating savings; the ideal unit for exacting commercial requirements. Inlets/outlets: (2) 2 in. dia. copper pipes. Overall dimensions: 10 ft. 8 in. L x 68 in. W x 52 in. H.



