

Safeline Stainless Steel Metal Detector

Mfg: Safeline Inc.

Model: STD16X14/55/300/1L/1/12/RC/RFI

Stock No. HDNW112.42a

Serial No.

Safeline Inc. Stainless Steel Metal Detector. Model STD16X14/55/300/1L/1/12/RC/RFI. Reference No. 12927-07. Maximum Product Clearance/Aperture Opening Above Belt: 15-5/8 in. wide by 12-1/2 in. high. Unit detects 2.5mm Non-Fe, 2.5mm Non-Magnetic SS, and 2.5mm Fe. Detector is Frame-Mounted. Includes a 14 in. W belt. Detector Specifications: 115/480 Volt, Pneumatically-Controlled Reject Device. Height at Product Inlet 46-1/2 in. Height at Conveyor 20 in. Baldor Industrial Motor. Mfg: Baldor. Motor Specifications: .5 hp, 1,725 rpm, 208-230/460 Volt, 2.1-2/1 Amps, 60 Hz, 3 phase, 56C Frame. Boston Gear 700 Series Drive Motor. Mfg: Boston Gear. Drive Specifications: .46 hp (input), 500 Torque lb-in (output), 40 Gear Ratio. Overall Dimensions: 168 in. L x 40 in. W x 76 in. H.



