

Neck Bander Model SS75

Mfg: Product Design

Model: SS75

Stock No. HDPH115.2a

Serial No. 024

Product Design Neck Bander.

- Model SS75
- S/N 024
- Motor General Electric, Model 5BPB56SAA101, 1 hp, 1,725 rpm,
- Overall dimensions 36 in. W, 40 in. L, 78 in. H.



75 Series
100 to 300 CPM

Designed for high speed tamper evident banding at 200 to 400 containers per minute (cpm) **the 75 Series Shrinksealer** also handles sleeving applications at 300 cpm dependant upon sleeve dimensions.

		75 Series
Sleeve Diameter Range		.375 to 3 1/2 inches (10 to 90 mm)

Sleeve Height Range .625 to 9 inches (15 to 225 mm)

Line Speed		100 to 300 cpm

Applications for both models:

Shrinksleeve Labeling - full height bodysleeve labels on bottles and jars providing primary package graphics. The sleeve label may also come up over the cap with a horizontal perforation for tamper evidence.

Tamper Evident Banding - such as those used for

- Neckbanding - applying a shrinksleeve around the upper portion of a container (and its closure)
- Full Height Safety Seals - full body, clear sleeves, protecting the paper label, container and covering the closure, such as on some vitamin jars.