

Prater Hammermill

Mfg: Prater

Model: M30

Stock No. FPPE089.6

Serial No. 391082

Prater Hammermill. Model: M30. S/N: 391082. Hammermill utilizes a 3/16-mesh screen over a mild steel cutting disc. Cutting disc diameter: 10 in. Premium Efficiency Motor, 20 hp, 3,525 rpm, 230/460 V, 47.2/23.6 amps, 60 Hz, 3 phase. Inlets: 3-1/2 in. dia. infeed port. Outlet: (2) 4 in. dia. bottom discharge port. Overall dimensions: 52 in. L x 32 in. W x 67 in H. Vibration Monitor, Model: 480.

