

Brush Washer with Stainless Steel Conveyor

Mfg:

Model:

Stock No. GAL01

Serial No.

Brush Washer with Stainless Steel Conveyor. Brush roller diameters: (4) 6 in., (10) 5 in. dia., (10) 4 in. dia., (4) 3 in. dia. Belt width: 6 in. Maximum aperture/clearance above belt: 7 in. W x 4 in. H. Dayton Washdown Duty Motor, 1 hp, 1725 rpm, 115/230 V, 13.6/6.8 amps, 60 Hz, single phase. Winsmith Speed Reducer, 15 ratio, 115 rpm (final). Teel Centrifugal Pump, Model: 1P788. Dayton Motor, model: 9R756, 1/2 hp, 3450 rpm, 115/230 V, 8.2/4.1 amps, 60 Hz, single phase. Conveyor infeed/exit height: 3 ft. Inlets: (1) 1 in. dia. FNPT. Outlets: (1) 3/4 in. dia. PVC tube (spray nozzles). Overall dimensions: 5 ft. 7 in. L x 1 ft. 8 in. W x 4 ft. 10 in. H.



