

## Admix Rotostat High-Speed High-Shear Mixer

Mfg: Admix

Model: 132XP124

Stock No. HDPH653.4a

Serial No.

Admix Rotostat High-Speed High-Shear Mixer. Model: 132XP124. Maximum batch size: 600 gal. Standard motor horsepower: 7.5. Flow rate: 2300 gpm. Propeller diameter: 7 in. Shaft dimensions: 2 in. x 54 in. L. Mounting flange has a 6-1/2 in. dia flange mount with (4) 1/2 in. dia. attachment holes at a center-to-center distance of 3-3/4 in. The unique patented revolving stator, when combined with the close clearance rotor, and high efficiency lower propeller, optimizes shear rates, pumping rates and particle size reduction. The interchangeability of different rotors, stators, and props provides maximum flexibility for fine tuning mixing applications and will never overshear sensitive materials or formulas. Overall dimensions: 11 in. dia. x 54 in. H.

