

## Frick LDB 26 Booster Compressor - 30 HP

Mfg: Frick

Model: LDB 26

Stock No: HDPW734.2

Serial No:

Frick LDB 26 Booster Compressor. Model LDB 26. Marathon electric motor, 30 hp, 1765 rpm, 230/460 V, 74/37 FLA, 60 Hz, 3 ph, 286T frame. Frick oil separator, Nat'l Board: 41687, MAWP: 150 psig at -20°F to 200°F, material: SA 53-S-GLB. Frick oil filter housing. S/N: NC-78012. MAWP: 300 psi at -20°F to 200°F. Package includes a simple to use, hard wire control panel, providing simple on/off of the screw compressor. This unit is for low temperature service only and includes liquid injection cooling. This is an excellent unit for a small freezer, spiral or a blast, or for a weekend service. Nominal capacity: 23.6 tons with R-717 at 25.4 BHP with a -40°F suction temperature and a 10 °F discharge temperature. Displacement: 257 cfm. Connections: 4 in. suction and 2 in. discharge. Estimated weight: 4,418 lbs. Overall dimensions: 8 ft. 9-1/2 in. L x 3 ft. 1 in. W x 5 ft. 10-5/8 in. H.





