

Hyster Forklift

Mfg: Hyster

Model: H80C

Stock No. GEEQ004.

Serial No. C005D16987

Hyster Forklift. Model: H80C. S/N: C005D16987. Motor stamping: F227A-605-W H 2. Fuel: gasoline. 6-Cylinder. Firing order: 1-5-3-6-2-4. Spark plug: Champion D16. Spark plug gap: set @ 0.025 in. Cylinder bore (as of 7-19-07): 3.3505 in. Intake valve diameter (as of 7-19-07): 1.517 in. Exhaust valve diameter (as of 7-19-07): 1.1985 in. Fork dimensions: 44 in. L x 5 in. W. (4) Front tires: GBC Powermaster Industrial, nylon, tubeless, 12-ply rating, size: 7.50-15 NHS. (2) Rear tires: MasterLift XtraWall PrimeX, tube type, size: 7.00-12 NHS. Overall dimensions: 12 ft. 6 in. L x 69 in. W x 84 in. H.





