

Stainless Steel Belt Conveyor – 14 in. W

Mfg:

Model:

Stock No: GM414.3

Serial No:

Stainless Steel Belt Conveyor – 14 in. W. Belt dimensions: 5 ft. 10 in. 1 ft. 2 in. KEB electric motor, ¼ hp, 1690 rpm, 230/460 V, 0.90/0.55 amps, 60 Hz, 3 phase. Pulley ratio: 2.27. Final rpm: 744. Infeed/exit height: 2 ft. 3-1/2 in. Overall dimensions: 6 ft. L x 2 ft. 3-1/4 in. W x 2 ft. 4 in. H. (ACN35)



