

## Stainless Steel Strainer Table

Mfg:	Model:
Stock No. HDWD179.6	Serial No.

### Stainless Steel Strainer Table.

- Inlets (2) 1 in. Outlets (1) 2 in.
- Conveyor belt measurements 36 in. W, 119 in. L.
- Cleat spacing 18 in. W, cleat height is 2 in.
- Gaps of conveyor belt for straining are 1/8 in.
- Motor with gearbox, Mfg. Boston. Frame 145TC, 2 hp, 208-230/460 volt, 6.5-6.2/3.1 amps, 1,725 rpm, 60 hz, 3 phase, Series F1096.
- Magnetek Motor. SN BP1-05230/115 volt, 3,450 rpm, 1 hp, 6.0/12.0 amps, 60 Hz, type CS, 3,450 rpm, 1 ph.
- Pump, Mfg. Atlas. Model 500 CR, SN 6941.
- Pump Inlets 1-1/2 in. Outlets (2) 1 in.
- Overall measurements 53 in. W, 128 in. L, 60 in. H.



