

Fristam Centrifugal Pump

Mfg: Fristam

Model: FP3551 250

Stock No: HDDF274.5

Serial No: 355168470

Fristam Centrifugal Pump. Model: FP3551 250. S/N: 355168470. 316 stainless steel. Capacity: 560 gpm @ 6 psi and 15 tdh. (1) 8 in. dia. impeller. Baldor Industrial Motor, 10 Hp, 1725 Rpm, 208-230/460 V, 28-26/13 A, 60 Hz, 3 Phase. Inlet: (1) 3 in. S line fitting. Outlet: (1) 2-1/2 in. S line fitting. Applications include, but are not limited to, bottling, cleaning applications/CIP, de-alcoholization, distillation, emulsifying, evaporation, mechanical separation, reverse osmosis, inline mixing, water conditioning, transfer filtration, extraction, dosing, dialysis, de-gassing, carbonizing, homogenizing, and fermentation. Overall dimensions: 2 ft. 8 in. L x 1 ft. 3 in. W x 1 ft. 4 in. H. (ACN74).





