

## Warren Rupp Stainless Steel Diaphragm Pump

Mfg: Warren Rupp

Model: SSA2-A

Stock No. HDDP154.16

Serial No.

Warren Rupp Stainless Steel Diaphragm Pumps. Model: SSA2-A. Displacement Per Stroke: 0.43 gallons. Maximum Flow per minute: 140 gallons. Maximum solids handling: 2 in. Maximum Discharge pressure: 125 psi. Pipe size: 2 in. Overall dimensions: 21 in. L x 17 in. W x 26 in. H. (Spare parts available). Complete with SA2-A Flap Valve. Flap valve SA Series Sandpiper pumps are especially recommended for slurries and liquids with suspended solids. Flap-valves allow passage of suspended line-size solids without damage. Variable discharge porting options available on the 3 in. pump model.

