

Tri Clover Tri-Blender

Mfg: Tri Clover

Model: F4329MD

Stock No. HDFD370.39a

Serial No. R8872

Tri Clover Tri-Blender. Model: F4329MD. S/N: R8872. Maximum dry ingredient capacity: 350 lbs per minute. 316 stainless steel wetted parts with quick-couple Tri-Clamp® connections. Impeller diameter: 9-1/2 in. Reliance Electric Motor, 20 hp, 3510 rpm, 230/460 V, 50/25 amps, 60 Hz, 3 phase. Final speed: 2340 rpm. Featuring fast, uniform, and continuous material absorption, the Tri Clover Tri-Blender is designed to thoroughly and efficiently batch blend dry ingredients and liquids. Benefits include: minimized production time, minimal lumping and foaming of product associated with air pockets resulting from conventional mixing equipment, easy of portability and ease of integration with existing systems. Inlet: 21 in. dia. x 15 in. H. (funnel infeed), (1) 2 in. dia. S-line fitting. Outlet: (1) 3 in. dia. S-line fitting. Overall dimensions: 3 ft. 2 in. L x 1 ft. 8 in. W x 2 ft. 7 in. H.



