

Tri Clover PRS125 Positive Displacement Pump

Mfg: Tri Clover

Model: PRS125-R3-TC1-4-SL-S

Stock No.: JMB522B

Serial No.: Z1347

Tri Clover PRS125 Positive Displacement Pump. Model: PRS125-R3-TC1-4-SL-S. S/N: Z1347. Flow rate for new pump is 100 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Seal option: Single mechanical seals. Teco electric motor, 5 hp, 1750rpm, 230/460 V, 13/6.5 amps, 60 Hz, 3 phase. Reliance Electric gear drive. Tri-Clover positive pumps handle high viscosity products at elevated GPM and pressure ratings, provide longer seal and rotor life, reduce maintenance costs and downtime, perform effectively on suction lift service, and handle liquids and semi-solids with entrained vapors. Products include: liquid sugar, tacky products like corn syrup, and viscous products. Inlet: (1) 9 in. L x 2-1/2 in. W rectangular infeed. Outlet: (1) 3 in. dia. threaded fitting. Overall dimensions: 4 ft. 1 in. L x 1 ft. 9-1/2 in. W x 2 ft. H. (ACN139a)



