

Depositor - Stainless Steel Conveyor

Mfg:

Model:

Stock No. HDNP077.6

Serial No.

(2) Depositor - Stainless Steel Conveyors. Conveyor #1: 65 in. L x 46 in. W. (Mesh is 40 in. W). (9) Sprayer outlets. This conveyor does not have a motor. Conveyor #2: Baldor Motor, 3 phase. Cat No. VWDM3554, Spec. 35H828X623. Frame 56 C, Ser. F890, 1-½ hp, 208-230/460 V, 4.6-4.2 amps, 1,725 rpm, 60 Hz. Rating is 40 ° C. amb cont. US Electric gear box, frame 26, type QC, Max input hp: 1.5 at 1,750 rpm, Gear ratio 30 v, SF 1.0, Max output torque 1,260. Id No. 5587004F. Has a sprayer. Conveyor mesh: 65 in. L x 46 in. W. Overall measurements: 88 in. L x 70 in. W x 53 in. H.



