

American Container Handling Systems, Inc. (ACHS) Incline Belt Conveyor

Mfg: American Container Handling Systems

Model:

Stock No: KMCR81.7

Serial No:

American Container Handling Systems, Inc. (ACHS) Incline Belt Conveyor. Belt width: 13 in. Cleat height: 2 in. Feet per minute: 94. Discharge height: 9 ft. 9 in. Distance from floor to bottom of the discharge chute: 99 inches. Stainless steel frame with castor wheels. Product inlet hopper. Unit will lower to go through doorways and make it easier to truck. Dura-Drive Plus brand motor drive 1.36/2 HP, 3330 RPM, 575V, 1.7 Amps, 60 Hz, type 5.3, S/N: 30974-1. Allen Bradley VFD speed controller. Overall dimensions: 12 ft. L x 5 ft. 3 in. W x 10 ft. H.



