

1997 RVS Vertical Ammonia Recirculator Package – 48 in. Dia. x 10 ft. H

Mfg: RVS

Model:

Stock No: KWBF004

Serial No: 97671

1997 RVS Vertical Ammonia Recirculator Package. S/N: 97671. National Board: 10199. Approximate capacity: 950 gallons. Inside straight-wall dimensions: 48 in. dia. x 10 ft. H. Refrigerant: R-717 (Ammonia). MAWP: 250 psi at 300°F. MDMT: -20° at 250°F.

(2) 1997 Cornell centrifugal pumps, Model: 2CB-5-4. S/N's: 101709 10.38, 101710 10.38. Flow rate for new pump is 180 gpm with required horsepower and pressure. Discuss with salesperson your process to determine if this refurbished pump should handle your specific duty. Impeller dia: 10.38 in. (2) Baldor industrial pump motors: 5 HP, 1760 rpm, 230/460 V, 13.6/4.8 amps, 60 Hz. 3 phase.

RVS oil pot: S/N: L25747, MAWP: 300 psi at 150°F, MDMT: -20°F at 300 psi. Radius: 2:1 elliptical ends. Inlets: (1) 6 in. dia. port, (2) 2 in. dia. port, (1) 1 in. dia. port. Outlets: (1) 6 in. dia. port, (2) 4 in. dia. port, (2) 1 in. dia. ports, (1) 1-1/2 in. dia. port, (1) 3/4 in. dia. port. Overall dimensions: 6 ft. 4 in. L x 5 ft. 9 in. W x 18 ft. 2 in. H.







