

Frigid Coil 4-Fan Ammonia Evaporator– 10.5 Tons

Mfg: Frigid Coil

Model: HTS-464-1/3-LRT-IP

Stock No: KWBF509B

Serial No:

Frigid Coil 4-Fan Ammonia Evaporator. Model: HTS-464-1/3-LRT-IP. Capacity: rated at 10.5 tons at a 15°TD for a 35°F room. Refrigerant: recirculated R-717 (Ammonia). Tube material: Hot dipped, galvanized steel. (4) fans, dia: 22 in.(pictures show one fan removed). Air flow: 13,840 cfm. (4) fins per inch, material of construction: hot dipped, galvanized steel. Stainless steel covered, insulated drain pan. (4) Baldor industrial motors: 1/3 hp, 1140 rpm, 230/460V, 2.5-2.5/1.2 amps, 60 Hz, 3 phase. Inlets: (1) 2 in. Outlets: (1) 1 in. Approximate weight: 1560 lbs. Approximate overall dimensions: 11 ft. 5 in. L x 3 ft. W. x 3 ft. 8 in. H.





Note: One fan is missing.