

Crepaco Stainless Steel 3-Tank CIP System – 150 Gallon Ea.

Mfg: Crepaco

Model:

Stock No.: HDST118.31

Serial No.:

Crepaco Stainless Steel 3-Tank CIP System. (3) 150 gallon stainless steel CIP tanks. Inside tank dimensions: 2 ft. 10 in. dia. x 4 ft. 2 in. H. Inlets: (3) 2 in. dia. S-line fittings, (2) 1-1/2 in. dia. FNPT fittings. Outlets: (1) 2 in. dia. S-line fitting, (1) 2-1/2 in. dia. S line fitting, (1) 2-1/2 in. dia. overflow port. Overall dimensions: 3 ft. 5 in. dia. x 6 ft. 1 in. H.





1999 ITT Bell & Gossett shell and tube heat exchanger. S/N: 735491-01-1. Nat'l Bd: 68253. Heat transfer surface area: approx. 34.5 sq. ft. Capacity: 4.03 gallons. Shell and tube side MAWP: 150 psi @ 375 °F. Shell and tube side MDMT: - 20 °F @ 150 psi. Overall dimensions: 4 ft. 10 in. L x 1 ft. 10-1/2 in. W x 9 in. H.









APV Crepaco centrifugal pump. Model: 6V. S/N: 6V-84. Flow rate for new pump is 140 gpm with required horsepower and pressure. Impeller diameter: 5 in. Marathon electric motor, 7-1/2 hp, 3530 rpm, 230/460 V, 19/9.5 amps, 60 Hz, 3 phase. Inlet: (1) 2-1/2 in. dia. S-line fitting. Outlet: (1) 1-1/2 in. S-line fitting. Overall dimensions: 1 ft. 10-1/2 in. L x 10 in. W x 1 ft. 2 in. H.





Crepaco control panel. Dwg: PD581. Ref No: DE-3. Power supply: 115 V, 15 amps, 60 Hz, 3 phase. Overall dimensions: 1 ft. L x 3 ft. 8 in. W x 4 ft. 7 in. H.





Also includes chart recorder, thermocouples, air operated sanitary valves, Magna control valves, and computerized controllers and sensors.

