

## RVS Shell and Tube Ammonia Chiller Unit – 25 tons

Mfg: RVS

Model: -

Stock No.: LKBA402.

Serial No.: 93944, 93945

RVS Shell and Tube Ammonia Chiller . Certified by Refrigeration Valves and Systems Corp. (RVS) Bryan, Texas USA. Nat'l Bd.: 6341. Shell side: MAWP 250 PSI at 200 F, MDMT: -20F at 250 PSI. Tube side: MAWP 150 PSI at 200F, MDMT: -20F at 150 PSI. S/N: 93944. Year built: 1993. RVS Surge Drum: Nat'l Bd. 6342, MAWP: 250 PSI at 200F, MDMT: -20F at 250 PSI, S/N: 93945, year: 1993. These are used to chill a water/glycol stream with ammonia refrigerant. Overall dimensions: 14 ft. 6 in. L x 55 in. W x 80 in. H.



← Installed picture. This was removed from a major US food processing line closure in Arkansas USA. The control panel, pump, and small yellow tank shown will not be included. See pictures below for the components as received at our Hearne, Texas facility.



