

Buffalo Grinder/Extruder

Mfg: Buffalo

Model:

Stock No. KLPC323.3a

Serial No.:

Buffalo Grinder/Extruder. Screw dimensions: 6 in. diameter x 17 in. L. Baldor Industrial Motor, 25 hp, 1760 rpm, 230/460 V, 64/32 amps, 60 Hz, 3 phase. Product inlet: (1) 7 in. L x 6 in. oval infeed. Outlet: (1) 8 in. diameter die with 1/4 in. diameter perforations. Overall dimensions: 65 in. L x 23 in. W x 52 in. H.



