







#### **Features and Benefits**


- **Sensorless Vector** The MA7200 has precise speed and torque control for the most demanding system performance and simple set-up through an auto-tuning function. It can be operated in sensorless vector or V/Hz mode to match the user's specific application.
- **Graphical LCD Operator** The MA7200 offers easily read parameters and status in plain English text on a 2 line by 20 character lighted LCD, eliminating the need to memorize parameters the user can set up the drive without an instruction manual! Straight forward monitoring of drive status through the operator is also available, which simplifies set-up and troubleshooting.
- **Parameter Copy** No extra hardware is required on this drive. The copy feature is included as standard in the keypad. Simple cloning of the drive program is available, making it perfect for the OEM.
- Flexible Input/Output Options The MA7200 offers Sink or Source Selectable Digital Inputs 4 Preset, 4 User Programmable, 16 Preset Speeds, 2 Analog Inputs, 2 Analog Outputs, 3 Multi-Function Output Contacts 1 Form C Relay, 1 Form A Relay, and 1 Open Collector Output.
- **Built-in PID Control -** The MA7200 has scalable PID feedback for accurate system regulation.
- **Powerful Programming Options** The MA7200 allows the user to set up basic parameters for simple tasks or take advantage of advanced features for demanding applications.
- **Simple PLC** The MA7200 can set custom run patterns for multiple machine cycles.
- **Communications** The MA7200 has Modbus RTU as a standard. The user can control, program and monitor the drive(s) over an Industrial Network. Other protocols are also available.
- PG Interface Built-in The MA7200 has Speed Control Accuracy of 0.1%.
- User Selectable V/F Curves + S Curve area available.
- **Motor/Drive Systems** Pair the MA7200 with a TECO-Westinghouse motor for single source reliability.



**Aggregate / Conveyor Application** 



**Oil Pump Application** 



# **Specifications**

Output	MAA 7200 NEMAA 1	208 - 230V 1 - 40 HP Constant Torque				
	MA7200 NEMA 1	380 - 460V				
	Maxima ya Valta a a	230 Volt 3-Phase, 208 - 230V				
Characteristics	Maximum Voltage	460 Volt 3-Phase, 380 - 460V				
	Rated Output Frequency	0 - 400Hz				
	Output Frequency Resolution	0.01Hz				
	Rated Input Voltage	230 Volt 1 - 3 HP 1/3-Phase, 208 - 230V, 50/60Hz				
	& Frequency	5 - 40 HP 3-Phase, 208 - 230V, 50/60Hz				
Power Supply	' '	460 Volt 1 - 75 HP 3-Phase, 380 - 460V, 50/60Hz				
	Voltage Fluctuation	10%, -15%				
	Frequency Fluctuation	+/-5%				
	Control Mode	Selectable Sensorless Vector, V/Hz, V/Hz				
		with PG Feedback				
	Operation Mode	English LCD Display				
	Carrier Frequency	Programmable: 2.5 - 15kHz				
	Frequency Control Range	0.5 - 400Hz				
	Frequency Accuracy	Digital Command: +/-0.01% (+14°F - 104°F)				
		Analog Command: +/-1% (77°F+/-14°F) +/-0.5% (Sensorless Vector)				
Control	Speed Control Accuracy	+/-0.1% (V/Hz with PG Feedback)				
Characteristics	Frequency Command	Digital Command: 0.01Hz				
Characteristics	Resolution	Analog Command: 0.06/60Hz				
		Constant Torque: 150% Rated Output Current for 60 Sec.				
	Overload Capacity	Variable Torque: 110% Rated Output Current for 60 Sec.				
	Frequency Setting Signal	0 - 10VDC, 4 - 20mA				
	Accel/Decel Time	0.0 - 6000 Sec. (Independent Accel/Decel Time Settings)				
	Number of V/F Patterns	15 Preset V/F Patterns, 1 Custom V/F Pattern				
	Braking Torque	Approximately 20%				
	Stall Provention	Stall Prevention at Acceleration/Deceleration and				
	Stall Prevention	Constant Speed Operation				
	Instantaneous Overcurrent	200% of Rated Output Current				
	Motor Overload Protection	Electronic Overload Protection				
	(230V Series)	Motor Coasts to a Stop if Inverter Bus Voltage				
	Overvoltage (450)/5	exceeds 410VDC				
	(460V Series)	Motor Coasts to a Stop if Inverter Bus Voltage				
Protective	(000)(5 1 )	exceeds 820VDC				
Functions	(230V Series)	Motor Coasts to a Stop if Inverter Bus Voltage drops to				
	Undervoltage (460) (Sories)	200VDC or below				
	(460V Series)	Motor Coasts to a Stop if Inverter Bus Voltage drops to 400VDC or below				
	Momentary Power Loss	Motor Coasts to a Stop after Momentary Power Loss				
	Widifferitary Fower Loss	lasting over 15ms				
	Overheat Protection	Protected by Thermistor				
	Ground Fault	Protected by DC Current Sensor				
	Power Charge	Charge Lamp stays ON until Bus Voltage drops				
	Indication (LED)	below 50VDC				
	marcador (LLD)	00.01.00100				

	Control Power	24VDC				
	Speed Reference Supply	·				
	Analog Input	0 - 10VDC, Input Impedance 20k Ohms				
		4 - 20mA, Input Impedance 250 Ohms				
		External Speed Potentiometer, 0 - 10VDC,				
		2k Ohms Minimum, .5 Watt				
Control	Auxiliary Analog Input	1 Programmable, 0 - 10VDC, Input Impedance 20k Ohm				
Connections	Analog Outputs	2 Programmable, 0 - 10VDC				
	Digital Inquite	8 Digital Inputs (4 Programmable): Positive or				
	Digital Inputs	Negative Control Logic				
	Digital Outputs	2 Programmable Form C Relays, 250VAC, 1 Amp or 30VDC,				
		1 Amp Programmable Open Collector, 48VDC, 50mA				
	Serial Communications	RS-485 Port, MODBUS Protocol				
	Location	Indoor (Protected from Dust and Corrosive Gases)				
	Ambient Temperature	+14 to 104°F (Not Frozen)				
Environmental	Storage Temperature	-4 to 140°F				
Conditions	Humidity	<90% RH (Non-Condensing)				
	Vibration	<1000m, 5.9m/s2 (0.6G)				
Certifications/	UL, cUL, CE					
	EN50081-2 (Requires exte	ernal EMI/RFI Filter)				
Compliance	EN50082-2					



A Complete Line of Accessories for the MA700. Noise filter, AC Reactor, PROFIBUS Board, Breaking Resistor, Analog Operator, Keypad Extension Cable.

# **Dimensions**

## 230V 1/3-Phase


MODELNO	HP	DRIVE AMPS	DIMENSIONS (Inches)		APPROX.	
MODEL NO.	CONSTANT TORQUE	CONSTANT TORQUE	HEIGHT	WIDTH	DEPTH	WT. (lbs.)
MA7200-2001-N1	1	4.8	8.54	5.20	5.65	6
MA7200-2002-N1	2	6.4	8.54	5.20	5.65	6
MA7200-2003-N1	3	9.6	11.00	5.51	6.95	9

#### **230V 3-Phase**

MODELNO	HP	DRIVE AMPS	DIMENSIONS (Inches)			APPROX.
MODEL NO.	CONSTANT TORQUE	CONSTANT TORQUE	HEIGHT	WIDTH	DEPTH	WT. (lbs.)
MA7200-2005-N1	5	17.5	11.00	5.51	6.95	9
MA7200-2007-N1	7.5	24	11.81	8.32	8.46	13
MA7200-2010-N1	10	32	11.81	8.32	8.46	13
MA7200-2015-N1	15	48	14.17	10.43	8.86	27
MA7200-2020-N1	20	64	14.17	10.43	8.86	27
MA7200-2025-N1	25	80	14.17	10.43	8.86	29
MA7200-2030-N1	30	96	25.45	10.60	10.91	67
MA7200-2040-N1	40	130	25.45	10.60	10.91	67

## **460V 3-Phase**

MODELNO	HP	DRIVE AMPS	DIMENSIONS (Inches)			APPROX.
MODEL NO.	CONSTANT TORQUE	CONSTANT TORQUE	HEIGHT	WIDTH	DEPTH	WT. (lbs.)
MA7200-4001-N1	1	2.6	8.54	5.20	5.65	6
MA7200-4002-N1	2	4	8.54	5.20	5.65	6
MA7200-4003-N1	3	4.8	11.00	5.51	6.95	9
MA7200-4005-N1	5	8.7	11.00	5.51	6.95	9
MA7200-4007-N1	7.5	12	11.81	8.32	8.46	13
MA7200-4010-N1	10	15	11.81	8.32	8.46	13
MA7200-4015-N1	15	24	14.17	8.32	8.86	27
MA7200-4020-N1	20	32	14.17	10.43	8.86	27
MA7200-4025-N1	25	40	14.17	10.43	8.86	29
MA7200-4030-N1	30	48	14.17	10.43	8.86	29
MA7200-4040-N1	40	64	25.45	10.60	10.91	67
MA7200-4050-N1	50	80	25.45	10.60	10.91	67
MA7200-4060-N1	60	96	29.39	12.13	11.11	102
MA7200-4075-N1	75	128	29.39	12.13	11.11	102





5100 N. IH-35 Round Rock, Texas 78681 1-800-279-4007

www.tecowestinghouse.com