

## Ammonia Surge Drum - 16 Gallon

Mfg:

Model:

Stock No.: MDBC262C

Serial No.: 0S-1764

Ammonia Surge Drum. S/N: 0S-1764. Approximate capacity: 16 gallons. Inside straight wall dimensions: 11 in dia. x 3 ft. 2 in. L. Refrigerant: R-717. MAWP: 250 PSI @ 650° F. MDMT: - 20° F @ 250 PSI. Head thickness: .250 in. Shell thickness: .250 in. Inlets/outlets: (2) 2 in. dia. ports. Overall dimensions: 5 ft. L x 3 ft. W x 1 ft. H.



