

Galvanized Steel Screw Auger Conveyor – 9 in. Diameter

Mfg:

Model:

Stock No: KWBF251.5

Serial No:

Galvanized Steel Screw Auger Conveyor. Auger dimensions: 9 in. dia x 97 ft. Pitch: 9 in. Dayton electric motor, 2 hp, 1725 rpm, 208-230/460 V, 6.2-5.8/2.9 amps, 60 Hz, 3 phase. Dodge Ti-gear speed reducer, ratio: 25.64, rpm out: 67 (final). Inlets: (1) 10 in. x 10 in. port. Outlets: (1) 10 in. x 10 in. port. Overall dimensions: 97 ft. 6 in. L x 1 ft. 3 in. W x 2 ft. 6 in. H.







