

## Langsenkamp Pulper/Finisher

Mfg: Langsenkamp

Model:

Stock No. 105.L33202.30

Serial No. 33202-001

Langsenkamp Pulper/Finisher. S/N 33202-001. Stainless steel. Cylindrical screen chamber: 11 in. dia x 38 in. L. Tyler screen mesh size: 10. Paddles: (2). Product intake: 10 in. x 13 1/2 in. Liquid outlet: 2 in. Pomace outlet: 3 3/4 in. x 3 1/4 in. US Electrical Motor, 7-1/2 hp, 220/440 V, 60 Hz, 3 phase. Final speed: 825 rpm. Pulpers are designed for the separation of liquids and solids by means of paddles rotating concentrically within a cylindrical screen. The liquid and desired amount of solids pass through the screen. The balance of the solids (pomace) is discharged through a large non-plugging port. Dryness of the pomace with a given screen can be controlled by the paddle speed, pitch, clearance, or feed rate. Overall dimensions: 81 in. L x 30 in. W x 46 in. H.



