

Howe Corporation Rapid Freeze Flake Ice Machine

Mfg: Howe Corporation

Model: 100-EA

Stock No: MDBC302

Serial No: 5189

Howe Corporation Rapid Freeze Flake Ice Machine. Model: 100-EA, S/N: 5189. Stainless steel drum. Refrigerant: flooded ammonia. Rated production capacity: 20,000 lbs. per day with respective water and air temperatures of 70°F and 90°F and a water flow of 1.65 gpm. Refrigeration requirements: 170,500 BTUH/Hr. Inside straight-wall dimensions: 3 ft. dia. x 4 ft. 4 in. H. Howe Corporation surge drum. Nat'l Bd No. 5609. Inside straight-wall dimensions: 1 ft. 8 in. dia. x 2 ft. 3 in. L. MAWP: 150 psi @ 650 °F. Graymills electric motor, 1/8 hp, 3450 rpm, 115-230 V, 60 Hz, single phase. Inlets: (1) 3 in. dia. flanged port. Outlets: (1) 9-1/2 in. L x 9 in. W. Approximate shipping weight of flaker and surge drum: 3,075 lbs. Overall dimensions: 5 ft. 11 in. L x 4 ft. 8 in. W x 7 ft. 10 in. H.(ACN335-88).





