

1998 JBT FoodTech FMC Fresh n Squeeze® Multi-Fruit Juicer

Mfg: JBT FoodTech

Model: MFJ-POS

Stock No: MDFC031.1

Serial No: 81003002

1998 JBT FoodTech FMC Fresh'n Squeeze® Multi-Fruit Juicer. Model: MFJ-POS. S/N: 81003002. Approximate processing capacity: 80-120 quarts / hr., or 20 fruit / min. Electrical requirements (USA): 115 volt. As a juicer that achieves the highest yields at reasonable speeds, the unique design of the Fresh'n Squeeze® allows the handling of most of the world's citrus fruit varieties including oranges, grapefruit, lemons, limes and tangerines. Reliance electric motor, 1.0 hp, 1725 rpm, 115/230 V, 13.6 amps, 60 Hz, single phase. Overall dimensions: 2 ft. 8 in. L x 2 ft. 3 in. W x 5 ft. 7 in. H.(ACN173).











