

Stainless Steel Belt Conveyor

Mfg:

Model:

Stock No.: L49104.2

Serial No.:

Stainless Steel Belt Conveyor. Belt width: 1 ft. Maximum aperture/clearance above belt: 10 in. W x 2-1/2 in. H. Baldor Electric Motor, 1/2 hp, 1725 rpm, 208-230/460 V, 1.8-1.6/0.8 amps, 60 Hz, 3 phase. Boston Gear Speed Reducer, ratio: 30, final speed: 57.5 rpm. Conveyor infeed/exit height: 7 ft. Overall dimensions: 13 ft. 2 in. L x 4 ft. W x 8 ft. 3 in. H.





