

## 2000 Niagara Blower Company "No-Frost"® Concentrator

Mfg: Niagara Blower Co.

Model: A40E

Stock No: MDFC066

Serial No:

2000 Niagara Blower Company "No-Frost"® Concentrator. Model: A40E. SN: 00-12983. (1) Marathon electric motor, .75 hp, 3450 rpm, 208-230/460 V, 60 Hz, 3 phase. (1) Marathon electric motor, 1/3 hp, 1725 rpm, 208-230/460 V, 60Hz, 3 phase. No-Frost® technology offers Glycol based refrigeration defrost and liquid desiccant dehumidification and is ideal for processing, packaging, and storage applications where consistent, frost free conditions are required. Features include: Permanent inhibition of 99.9% of airborne pathogens, moisture absorption from the air stream, and a sanitary, frost-free coil. Inlets: (1) 1 in. dia. Port. Outlet: (1) 1 in. dia. port. Overall dimensions: 5 ft. L x 3 ft. 5 in. W x 6 ft. H. (ACN560)







