

1999 Waukesha Model 60 Positive Displacement Pump

Mfg: Waukesha Cherry-Burrell

Model: 60 U1

Stock No: 42a.ME138a.5

Serial No: 24263599

1999 Waukesha Cherry Burrell 60 Positive Displacement Pump. Model: 60 U1. S/N: 24263599. Flow rate for new pump is 90 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. The model 60 U-1 has a 3-A sanitary rating with 316 stainless steel pump body, cover and shaft and features: easy cleaning and disassembly, three-way mounting options, and non-galling, Waukesha "88" alloy rotors. Maximum pressure: 200 psi. Maximum speed: 600 rpm. Temperature range: -40°F to 300°F. Seal option: single o-ring buna elastomers. Baldor industrial motor: 3 hp, 1750 rpm, 230/460 V, 8.2/4.1 amps, 60 Hz, 3 phase. ISR gear drive, 4.43:1 ratio, 395 rpm (final). Inlets / outlets: (2) 2-1/2 in. dia. S-line fittings. Typical product applications include: (confectionery) syrups, cream fillings, chocolate, (pharmaceutical / health care) pill pastes, emulsions, slurries (dairy), cottage cheese and yogurt. Overall dimensions: 3 ft. 2 in. L x 1 ft. 4 in. W x 1 ft. 6 in. H.(ACN116).



