

Ball Mill 2 ft. 8 in. dia. x 3 ft. ½ in. L.

Mfg:

Model:

Stock No: MASH047

Serial No:

Ball Mill Inside dimensions: 2 ft. 8 in. dia. x 3 ft. ½ in. L. Constant grinding action is provided for using porcelain balls as the grinding media with the surface area of each ball multiplying its effect. This mill features a high alumina brick lining with applications to include: chemicals, paints, coatings, and ceramics industries where the reliability and uniformity of output tolerances must maintain consistency. This unit was in prior service with Crane Plumbing in their porcelain process line. Cleveland Worm gear drive: 200-AT. No. L 11463. Series: 26. 2 Hp, 240 Rpm, 40-1 ratio. General Electric motor. (2) 12-3/4 in. x 8-3/4 in. opening covers. Overall dimensions: 8 ft. L. x 5 ft. 4-1/2 in. W. x 4 ft. 10 in. H.





