

## Stainless Steel Inclined Belt Conveyor

**Mfg:**

**Model:**

**Stock No.: MF-135.2a**

**Serial No.:**

Stainless Steel Inclined Belt Conveyor. Maximum aperture: 7 in. W. Baldor Electric Motor, 1/4 hp, 1725 rpm, 115 V, 6.2 amps, 60 Hz, single phase. Boston Gear 300 Series Speed Reducer. Conveyor infeed height: 2 ft. 4-1/2 in. Conveyor exit height: 3 ft. 4-1/2 in. Overall dimensions: 12 ft. 9-1/2 in. L x 1 ft. 2 in. W x 3 ft. 8 in. H.



