

Stainless Steel SWECO 3-Level Separator – 48 in.

Mfg: SWECO

Model: A/8922-B-1D

Stock No: MASH065

Serial No: 2047

Stainless Steel SWECO 3-Level Separator. Model: A/8922-B-1D. S/N: 2047. (3) 48 in. dia. product trays. Westinghouse motor: 1 Hp, 1155 rpm, 550 V, 1.36 A, 60/50 Hz, 3 Phase. Sweco separators offer maximum throughput and screening efficiency to many types products by accomplished vibration over a screen cloth with varieties of mesh sizes to fit specific applications. Products and actions addressed include: sizing for dry products to include: sugars, spices, feeds, and abrasives; “scalping” to remove unwanted, oversized particles to include metal bits, blood and bone material; gravity filtering and product recovery from slurries such as ceramics; and waste water cleanup which could include brewery waste, laundry waste, or many other effluent applications. This unit was in prior service with Crane Plumbing in their porcelain processing line. Top level discharge opening 16 in. L x 6 in. H. (1) 6 in. side outlet. (3) 8 in. discharge spouts. Unit weight 714 lbs. Overall dimensions: 4 ft. 5 in. L x 4 ft. 9 in. W x 4 ft. H.





