

## Scot Circulating Pump

Mfg: Scot

Model:

Stock No.: MDBC267B

Serial No.:

(2) Scot circulating pumps. Pumps are equipped with Keckley 4" Traps. Impeller size: 6.88 in. dia. Baldor electric motor, 5 hp, 1725 rpm, 208-230/460 V, 14.8-14.0/7.0 amps, 60 Hz, 3 phase. Inlet: (1) 4 in. dia. suction port with an 9 in. dia. flange and (8) 3/4 in. dia. thru holes at a center distance of 2-7/8 in. Outlet: (1) 3 in. dia. discharge port with a 7-5/8 in. dia. flange and (4) 3/4 in. dia. thru holes at a center distance of 4-3/8 in. Overall dimensions: 2 ft. 11 in. L x 1 ft. 1-1/2 in. W x 1 ft. 4 in. H.





