

## Steel Feeder/Hopper - 145 Cubic ft.

**Mfg:**

**Model:**




**Stock No: MRSP121**

**Serial No:**

Steel Feeder/Hopper – 145 cubic ft. capacity, w/ approximately 15 ft. stand. Equipped with: (1) pneumatic piston activated Plattco slidegate, model: UUS08852, (1) model: R, Roto-Bin-Dicator® for level sensing. (1) 3 ft. 2 in L x 1 ft. 9 in. W top access door. Inlet: (1) 10 in. L x 10 in. W port. Outlet: (1) 8 in. L x 8 in. W port. Overall dimensions: 5 ft. 10 in. L x 5 ft. 6 in. W x 15 ft. 4 in. H. (BH).







**BINDICATOR®**  
 ROTO-BIN-DICATOR®  
 WEATHER-TIGHT

LISTED  
 AND CONT. EQ.  
 985H

UL

**MODEL R**

SA

SWITCH: SP-DT, 1 HP 115 V.A.C., 2 HP 250 V.A.C.  
 SWITCH RATING: 20 AMP, 125, 250 or 480 V.A.C.  
 PILOT DUTY: 345 VA., 115 V.A.C., 690 VA., 230 V.A.C.  
 MOTOR: 110 V.A.C., 50/60 HZ., 4 WATTS

BINDICATOR COMPANY  
 PORT HURON, MICHIGAN 48060  
 MADE IN U.S.A.

COVERED BY ONE OR MORE OF THE FOLLOWING U.S. PATENTS  
 2,851,553 4,095,064 4,147,906 4,392,032 4,695,685

**TRD Manufacturing, Inc.**  
 A BIMBA Company

STROKE 5" x 9"

22-00481-331  
 S/N 03-74621 (L1)

125 PSI Air Max  250 PSI Air Max  400 PSI Hyd Max

**PLATTCO SLIDEGATE** MANUFACTURED IN U.S.A. BY PLATTCO CORP. PLATTSBURGH, NEW YORK 12501

MODEL NO. UUS080852

SERIAL NO. SG 1229

PATENT NUMBERS

**PLATTCO SLIDEGATE**

MODEL NO. UUS080852

SERIAL NO. SG 1229