

1992 Universal International, Inc. / Universal Industries Vertical Bucket Elevator

Mfg: Universal International, Inc. / Universal Industries

Model: U2-800

Stock No: MRSP127

Serial No: 74060-1

1992 Universal International, Inc. / Universal Industries Vertical Bucket Elevator. Model: U2-800. S.O: 74060-1. Capacity of free flowing material @ 85% Bucket fill: 800 ft³/h. Bucket spacing: 5 in. Bucket size: 7 in. L x 4 ½ in. W x 4 in. Deep. Infeed: 8 in². Discharge: 10 in². Belt width: 8 in. Belt speed: 168 FPM. Baldor Electric motor, 1 hp, 1725 rpm, 208-230/460 V, 3.6-3.4/1.7 amps, 60 Hz, 3 phase. Dodge torque arm speed reducer, ratio: 15.35. Final rpm: 112. U2 series bucket elevators applications include hot, abrasive, heavy, corrosive, hygroscopic and wet materials, and also features an exclusive "easy dump" design. (1) Access 10 in W x 6 in. H access door. Inlet: (1) 8 in. W x 8 in. H port, (1) 4 in. dia. side access port. Outlets: (2) 8 in. dia. port. Overall dimensions: 5 ft. 2 ½ in. L x 2 ft. 9 in. W x 18 ft. 6 in. H.



