

## 2001 Enerquip Shell and Tube Heat Exchanger

Mfg: Enerquip

Model:

Stock No. MFBB360C.

Serial No. 5363

2001 Enerquip Shell and Tube Heat Exchanger. S/N: 5363. Nat'l Bd: 3943. 3-A sanitary rated. 10 sq. ft. total surface area. 316 stainless steel. (42) 3/8 in. dia. x 30 in. L tubes. Two pass heat exchanger. Shell side MAWP @ 375 °F: 150 psig. Tube side MAWP @ 375 °F: 150 psig. Shell side MDMT @ 150 psig: -20 °F. Tube side MDMT @ 150 psig: -20 °F. Applications include processing milk and milk related products. Inlets: (1) 1 in. dia. NPT (male, media), (1) 2 in. dia. S-line fitting. Outlets: (1) 2 in. dia. S-line fitting. Overall dimensions: 9 in. dia. x 36 in. L.



