

## Warren Rupp Sandpiper® Double Diaphragm Pump

**Mfg: Warren Rupp**

**Model: PB1-A**

**Stock No: MRSP273.a**

**Serial No: 522605**

Warren Rupp Sandpiper® Double Diaphragm Pump. Model No. PB1-A. Serial No. 522605. Type: TGN-3-PP. Maximum recommended air pressure: 100 psi. (1) 1 in. flange inlet dia. (4) 5/8 in. dia. mounting holes. 2-1/4 in. adjacent. 3 in. opposite. (1) 1 in. flange outlet dia. (4) 5/8 in. dia. mounting holes. 2-1/4 in. adjacent. 3 in. opposite. (1) 3/4 in. FNPT airline inlet. (1) 3/4 in. air valve/center block. Overall dimensions: 1 ft. 4 in. L. x 11-3/4 in. W. x 1 ft. 10-1/2 in. H.



