

## Goulds G&L Series SST Centrifugal Pump

**Mfg: Goulds**

**Model: SST**

**Stock No: NOIP9007**

**Serial No:**

Goulds G&L Series SST Centrifugal Pump. Teco-Westinghouse motor 40 hp, 3550 rpm, 230/460 volts, 94/47 amps, 60 Hz, 3 phase. Inlet: (1) 3-5/8 in. dia. flange. 4 mounting holes 7/8 in. dia. 4-1/8 in. adjacent 5-1/2 opposite. Outlet: (1) 1-1/2 in. flange. 4 mounting holes 5/8 in. dia. 3-3/4 in. adjacent 3-7/8 in. opposite. Overall dimensions: 2 ft. 9-3/4 in. L. x 1 ft. 10 in. W. x 1 ft. 7-1/2 in. H.





3-PHASE INDUCTION MOTOR			
40 HP 2 P	FRAME 324JM	TEFC	
	NEMA DESIGN B	INS.CL. F	
TYPE AEEAJM	CONNECTION		
VOLTS 230/460 Hz 60	4 9 6	4 9 6	
AMPS 94 / 47 S.F. 1.05	8 5 7	8 5 7	
RPM 3550 AMB 40°C	2 3 1	2 3 1	
RATING CONT. CODE G	↑ ↑ ↑ ↑		
BEARINGS 6312C3 6212C3	230V LINE 460V LINE		
SER.NO. LL	MODEL NO. 324JM		
USABLE ON 208 V NETWORK AT 108 AMP.			
<b>TECO - Westinghouse</b> MOTOR COMPANY SCARBOROUGH, NEWARK			