

## Fristam FP-Series Centrifugal Pump

**Mfg: Fristam**

**Model: FP722-145**

**Stock No. NPPC153.**

**Serial No. FP7220010965**

Fristam FP-Series Centrifugal Pump. Model: FP722-145. S/N: FP7220010965. Capacity: 188 gpm. Impeller diameter: 5-1/2 in (145 mm). Seal option: double mechanical with water flush. Baldor Motor. 5 hp, 3450 rpm, 12/6 amp, 60 Hz, 3 ph. FP-Series centrifugal pumps are able to process abrasive products, are CIP-able and SIP-able, and are capable of product temperatures up to 400 °F. Inlets: (1) 2 in. s-line. Outlet: 1-1/2 in. s-line discharge. Overall dimensions: 28 in. L x 14 in. W x 19 in. H.



